
# DATA SHEET

### S4LFT1330-075

F-THETA STANDARD - FUSED SILICA 355 nm



#### **OUTLINE DRAWING**



All information contained in this data sheet is for information purposes only and is not binding. The content is subject to change at any time without notification, all information without guarantee. We reserve the right to make constructional changes in the course of product improvement. Copyright © Sill Optics GmbH • All rights reserved




## DATA SHEET

#### **SPECIFICATIONS**


| article number   | S4LFT1330-075                      |
|--|------------------------------------|
| design wavelength [nm]   | 355                                |
| effective focal length [mm]  | 329.3                              |
| working distance [mm]  | 260.5                              |
| max. entrance beam-Ø [mm]  | 14.0                               |
| aperture stop distance [mm]  | 36.0                               |
| scan area for a 2 mirror system with<br>mirror distance from lens housing for<br>mirror 2 / mirror 1 [mm x mm] | 210 x 210<br>26.0 / 46.0           |
| max. telecentricity error [°]  | 21.0                               |
| total transmission [%]   | > 97                               |
| absorption [ppm]   | not specified                      |
| lens material  | fused silica                       |
| LIDT (coating)   | 1.0 J/cm² per 1ns pulse<br>at 50Hz |
| SP and USP usable  | yes                                |
| weight [kg]  | 1.5                                |
| cover glass  | S4LPG4160-075                      |
| cleanliness  | not specified                      |

#### **SPOT**



spot diameter at 86.5% level for a Gaussian beam (M² = 1) with 14.0 mm diameter at  $1/e^2$ , clipped at 14.0 mm field size and mirror distances as given above for a two mirror scan system

#### **BACK REFLECTION POSITIONS**



#### **REMARKS**

The stated values are based on a vignetting of less than 1 %.

Effective focal length and working distance have a tolerance of +/- 1.5 %.

Absorption tolerance +/- 25 %. Absorption may increase. Correct cleaning establishes original condition.

All information contained in this data sheet is for information purposes only and is not binding. The content is subject to change at any time without notification, all information without guarantee. We reserve the right to make constructional changes in the course of product improvement. Copyright © Sill Optics GmbH • All rights reserved

